

Date \_\_\_\_\_

Customer code C- \_\_\_\_\_

Invoice address \_\_\_\_\_

Contact person \_\_\_\_\_

\_\_\_\_\_

Your reference \_\_\_\_\_

\_\_\_\_\_

Other delivery address \_\_\_\_\_

\_\_\_\_\_

Invoice address = delivery address

Quote

DECON E-DRIVE



Please add order form for the standard chair. Decon E-Drive is compatible with all manual Netti wheelchairs. Mounting on the Netti wheelchair is included – the standard wheels will remain with the manufacturer.

= Standard equipment

Item no.	Description	Price in €
D70001	<input checked="" type="checkbox"/> Decon E-Drive with standard configuration as stated below	5,769,-
D71016	<input type="checkbox"/> Mounting kit for Netti chairs	169,-
D70013	<input type="checkbox"/> Delivery with standard Netti mail wheels for wheel combination 24''+7'' incl. quick release and bushers (a constant change between Decon and Netti wheels is only possible as special adaptation)	59,-
D800	<input type="checkbox"/> Delivery with standard Netti mail wheels for other wheel combinations than 24''+7'' incl. quick release, bushers and other necessary parts (a constant change between Decon and Netti wheels is only possible as special adaptation)	Price on request
<b>Battery and charger</b>		
Standard	<input checked="" type="checkbox"/> NiMH battery with a max range of approx. 15 km	0,-
D70011	<input type="checkbox"/> Li-ion battery with a max range of approx. 25 km	682,-
Standard	<input checked="" type="checkbox"/> Battery charger 100-240V	0,-
D70021	<input type="checkbox"/> Power converter for car 12V	120,-
<b>User weight</b>		
Standard	<input checked="" type="checkbox"/> Max user weight 125 kg	0,-

D70031	<input type="checkbox"/>	Heavy duty version - max user weight 150 kg by 20", 22", 24" or 26" wheels Rims and spokes are made from a stronger material	220,-
--------	--------------------------	---	-------

Wheel size and accessories			
D71015	<input type="checkbox"/>	Anti-tippers (required except if combined with a universal device holder)	189,-
D71000	<input type="checkbox"/>	16" Flexel fine tread wheels	263,-
D71001	<input type="checkbox"/>	20" fine tread pneumatic wheels with aluminium push rims	263,-
D71002	<input type="checkbox"/>	22" fine tread pneumatic wheels with aluminium push rims	263,-
Standard	<input checked="" type="checkbox"/>	24" x 1 3/8 fine tread pneumatic wheels with aluminium push rims	0,-
D71003	<input type="checkbox"/>	26" x 1" fine tread pneumatic wheels with aluminium push rims (only for the Netti III family)	290,-
D71004	<input type="checkbox"/>	PU wheels (available for 20", 22", 24" and 26" x 1")	67,-
D71014	<input type="checkbox"/>	PU wheels wide (available for 22" and 24" x 1 3/8")	56,-
D71005	<input type="checkbox"/>	Spoke guards, transparent (available for 20"-26" wheels)	187,-



[A]



[B]

Driving unit			
Standard/ D71006	<input checked="" type="checkbox"/>	Joystick for user, swing-away arm [A] <input checked="" type="checkbox"/> Right <input type="checkbox"/> Left	0,-
D71007R/ D71007L	<input type="checkbox"/>	Joystick mounted for use by caregiver <input checked="" type="checkbox"/> Right <input type="checkbox"/> Left	0,-
D71008R	<input type="checkbox"/>	Attendant control instead of joystick [B] <input checked="" type="checkbox"/> Right	0,-
D71009R/ D71009L	<input type="checkbox"/>	Second joysticks for caregiver [2xA] <input checked="" type="checkbox"/> Right <input type="checkbox"/> Left	708,-
D71010R	<input type="checkbox"/>	Attendant control in addition to the joystick [A+B] <input checked="" type="checkbox"/> Right	675,-



		Mounting
Standard	<input checked="" type="checkbox"/>	Behind the back of the wheelchair, including bag for mounting
SPECIAL	<input type="checkbox"/>	For chairs with dynamic back unit a special holder for the battery under the frame must be requested

**Please note:**

- Netti 4U chairs adjusted in seat depth 500 mm require frame extension.
- The mounting of wide front wheels (min. 45 mm) is required.
- For chairs with seat width extension, please contact customer service.

**Specifications**

Motor	Yamaha motors: 24V 120W
Battery types	NiMH battery, 24V x 6.7Ah - range 15 km Li-ion battery, 25V x 11.8Ah - range 35 km
Wheel	7 kg
Total weight	16 kg (including NiMH battery) 17.5 kg (including Li-ion battery)
Total chair width	Netti 4U Family: Seat width approx. + 230 mm Netti III Family without frame extension: Seat width + 245 mm Netti III Family with frame extension*: Seat width +256 mm Netti III Family with 16" Decon E-Drive: Seat width approx. + 260 mm  E-Drive increases the total width with approx. 40 mm *Please note that frame extension is included in some options like Extra-long seat depth, dynamic back solutions etc. Please contact customer service for questions.
Wheel dimensions	16", 20", 22", 24", 26"
Air pressure	6 Bar, 600 kPa
Speed	0-6 km/t
Maximum range with fully charged battery	Approx. 15 km with NiMH battery/ Approx. 35 km with Li-ion battery in accordance with ISO 7176-4
Fuse	30 A (flat)

Max user weight	Up to 125 kg (for 16'': up to 100 kg)
Max user weight "Heavy-duty"	Up to 150 kg Rims and spokes are made from a stronger material
Max gradient	6°
CE mark	Complies with EU-Directive 93/42/EEC
Joystick	Contactless sensing by single-chip/ Std. fitted on right side swing-away arm.
Force alteration	By optional spring (for individual optimization)
USB charger	Auxiliary USB port (5V, 500 mA max.)
Display device	LCD (Vertical aligned)
Parameter setting	Onboard (joystick) / via PC (Smart Tune)
Battery charger	100 to 240V AC, 50/60Hz (standard) A power converter for car is available as accessory.
Rated power	37V. 26A (when charging)
Charging time	Normal charging time approx. 2-3 hours
Possible combinations	Please send us a request for a combination with other options of the selected wheelchair as some combinations might not be possible.